# IN-PAKT PRECISION CT



UNE COMPAGNIE SIKA

In-Pakt Precision CT is a pre-packaged, high performance, pumpable, non-shrink, cementitious grout for cold temperature applications. It is a cement-based, non-metallic, non-shrink grout containing well-graded, natural, fine aggregate and other carefully selected components. In-Pakt Precision CT meets ASTM C 1107, Type C grout and can be used at varying consistencies from dry pack to fluid in temperatures above -5 °C (23 °F).

#### **FEATURES & BENEFITS**

- Can be mixed and placed from dry pack, plastic and fluid consistencies using relatively low water:cement ratios
- **Excellent pumpability**
- Improved resistance to wash-out
- Achieves hardened properties in cold temperature conditions
- Very low permeability
- Non-corrosive, non-chloride, non-metallic
- Excellent resistance to freeze-thaw cycling and salt-scaling in the presence of de-icing salts
- All KING products are manufactured using ISO 9001:2015 Certified Processes

#### **USES**

- Grouting machinery base plates and column sole plates
- Grouting anchor bolts, dowels and hand rails
- Repair of pre-cast units
- Infill of pipes and sleeves in marine environments.

#### **PROCEDURES**

Surface Preparation: All surfaces to be in contact with In-Pakt Precision CT must be free from dust, oil, grease or any other foreign substances that may interfere with the bond of the material. Remove all delaminated or unsound concrete providing a roughened surface. To avoid freezing of the interface between the grout and the parent concrete, do not pre-wet the receiving surface. Pneumatically remove any free standing or other fine particles that may interfere with the bond between the grout and the substrate.

When temperatures are below -5 °C (23 °F), the temperature of the substrate, plates and grout must be warmed at 5 °C (40 °F) for 24 hours prior to placement. The temperature of the grouted area must be maintained above 0 °C (32 °F) for 24 hours after application.

Water Proportioning for Grout Consistency: The following amounts of water will produce the following grout consistencies:

Dry Pack - Approx. 2.5 L (0.66 US gallon) of water Plastic - Approx. 3.0 L (0.79 US gallon) of water Fluid - Approx. 4.0 L (1.0 US gallon) of water

Note: Water requirement varies with temperature. Increase water slightly as temperature rises and decrease water slightly as temperature decreases.

Mixing: Place 75% of required water into mixer and slowly introduce entire bag of In-Pakt Precision CT. Add balance of required water slowly while mixer is running, not exceeding maximum recommended volume of water. Continue mixing for a minimum of 3 minutes and stop only when material has obtained a consistent homogeneous mix.

## Placing:

Dry Pack - Firmly press or ram In-Pakt Precision CT into place using metal or hardwood tamping tools and a mason's trowel. Grout consistency when pressed into a firm ball should display no cracking or excessive surface moisture.

Plastic - Rod into place or trowel into areas where material can not flow into place. Grout consistency should be similar to that of a masonry mortar (between 100% and 115% flow, ASTM C 1437).

Fluid - In-Pakt Precision CT may be poured or pumped into place. Pour continuously with adequate head pressure or pump into place ensuring that all voids are completely filled. Formwork joints should be caulked with suitable material. Adequately vent high points to allow entrapped air to escape.

### **CURING**

A resin based liquid membrane curing compound approved for use in cold weather conditions that complies with ASTM C 309 should be applied immediately after grout reaches final set.

#### **TECHNICAL DATA**

The following data is representative of typical values achievable under laboratory conditions. Results in the field may vary.

	DRY PACK	PLASTIC	FLUID
WET DENSITY ASTM C 138			
7.01		2127 kg/m³ (132 lb/ft³)	
FLOW ASTM C 14	37	4400/#	4500/
		110%*	> 150%
VOLUME O	2.5 L (0.66 US gallo	3.0 L	4.0 L on) (1.0 US gallon)
WORKING		60 minutes	60 minutes
SET TIME ASTM C 19 Initial Final	1 (METHOD A)	3.0 hours 3.5 hours	5.5 hours 7.0 hours
COMPRESSIVE STRENGTH			
ASTM C 10 1 Day	9	25 MPa (3625 psi)	15 MPa (2175 psi)
3 Day	40 MPa (5800 psi)	30 MPa (4350 psi)	21 MPa
7 Day	45 MPa	45 MPa (6500 psi)	35 MPa
28 Day	55 MPa (8000 psi)	55 MPa	40 MPa (5800 psi)
COMPRESSIVE STRENGTH ASTM C 109 [at 5 °C (40 °F)]*			
1 Day		5 MPa (725 psi)	
3 Day		25 MPa (3625 psi)	
7 Day		30 MPa (4350 psi)	
28 Day		40 MPa	

(5800 psi)

## **IN-PAKT PRECISION CT**



UNE COMPAGNIE SIKA

DRY PACK PLASTIC FLUID

SPLITTING TENSILE STRENGTH ASTM C 496

**28 Day** 4.0 MPa 3.5 MPa (580 psi) (505 psi)

**BOND STRENGTH BY SLANT SHEAR** 

**ASTM C 882** 

**28 Day** 14.0 MPa 12.0 MPa

(2030 psi) (1750 psi)

**MODULUS OF ELASTICITY** 

**ASTM C 469** 

28 Day 26.0 GPa 19.5 GPa

(3.8 x 10<sup>6</sup> psi) (2.8 x 10<sup>6</sup> psi)

HARDENED HEIGHT CHANGE

**ASTM C 1090** 

**28 Day** 0.10% 0.02%

ABSORPTION

ASTM C 642

**28 Day** 8.2% 13.0%

FREEZE-THAW RESISTANCE

**ASTM C 666** 

**28 Day** 100% 107%

(Excellent durability factor)

**SALT-SCALING RESISTANCE** 

**ASTM C 672** 

**25 Cycles** 0.02 kg/m<sup>2</sup> 0.04 kg/m<sup>2</sup>

(0.004 lb/ft<sup>2</sup>) 0.008 lb/ft<sup>2</sup>)

**50 Cycles** 0.22 kg/m<sup>2</sup> 0.20 kg/m<sup>2</sup>

 $(0.05 \text{ lb/ft}^2)$   $(0.04 \text{ lb/ft}^2)$ 

## **OPTIMUM PERFORMANCE**

- · Not recommended for areas of extremely high vibration
- For void filling applications larger than 50 mm (2 inches), use MS-S10 SCC or RS-S10 SCC
- Contact your local KING Technical Representative for recommendations or information on uses or conditions not listed

 YIELD
 PLASTIC
 FLUID

 25 KG (55 lb)
 0.013 m³
 0.014 m³

 (0.46 ft³)
 (0.49 ft³)

#### **PACKAGING**

In-Pakt Precision CT is normally packaged in 25 KG (55 lb) triplelined bags and polywrapped on wooden pallets. All KING products can be custom packaged to suit specific job requirements.

#### STORAGE AND SHELF LIFE

Material should be stored in a dry, covered area, protected from the elements. Unopened bags have a shelf life of 12 months.

#### SAFETY PROCEDURES

In-Pakt Precision CT contains Portland cement. Normal safety-wear such as rubber gloves, dust mask and safety glasses used to handle conventional cement based products should be worn. Safety Data Sheets are available upon request.

Warranty: This product is designed to meet the performance specifications outlined in this product data sheet. If the product is used in conditions for which it was not intended, or applied in a manner contrary to the written recommendations contained in the product data sheet, the product may not reach such performance specifications. The foregoing is in lieu of any other warranties, representations or conditions, expressed or implied, including, but not limited to, implied warranties or conditions of merchantable quality or fitness for particular purposes, and those arising by statute or otherwise in law or from a course of dealing or usage of trade. [REV.0010\_2458717.5]

<sup>\*</sup>Laboratory conditions with material and ambient temperatures kept at 5 °C (40 °F).